

Product Information

Technical Data Sheet

Fluoro Silicone Rubber Compound

FE-350U

FEATURES

- 50 Shore A hardness
- White
- Highly resistant to high and low temperature and solvents

BENEFITS

- Pigmentable
- Wide service temperature
- Suitable for molding process
- Low compression set

A FE-350U fluoro silicone rubber designed for use in a variety of molded goods requiring high and low temperature and solvent resistance

1. APPLICATIONS

Special molded rubber parts such as O-ring, gasket, packing and others for requiring high and low temperature and solvent resistance.

2. TYPICAL PROPERTIES

FE-350U

Properties	Standard	Unit	Value
Appearance	ASTM E1767		White
Williams Plasticity	ASTM D926	mm/100	210
Specific gravity	ASTM D792		1.44
Hardness	ASTM D2240	Shore A	50
Tensile Strength	ASTM D412	MPa	9.7
Elongation at break	ASTM D412	%	430
Tear strength, Type C	ASTM D624	KN/m	26
Linear Shrinkage	JIS K6249	%	3.4
Compression set (175°C, 22hr)	ASTM D395	%	10

Properties obtained using 0.8 part of SC-8B(50P)(2,5-bis(tert-butylperoxy)-2,5-dimethyl hexane) on 2mm thick slabs; molded 10 minutes at 170°C and post-cured 4hours at 200°C.

*** Specification writers :** These values are not intended for use in preparing specifications.

3. HOW TO USE

FE-350U is most suitable for blending or pigmenting, milling with a two-roll mill process. Milling time should be carefully decided to secure uniformity of silicone rubber. When molding, Grace Continental Korea recommends using 0.8 to 1.2 part of SC-8B to 100 parts of silicone rubber. Standard cure temperature is 170°C, and its cure time depends on thickness of final products. Post cure condition would be 4 hours at 200°C after molding in most case.

For more detailed information on the use of FE-350U silicone rubber, please contact Grace Continental Sales.

4. PACKING

FE-350U is available in 20kg boxes

**Fluoro Silicone
Rubber Compound**

FE-350U

5. HANDLING PRECAUTIONS

Product safety information required for safe use is not included. Before handling, read product and safety data sheet.

6. USABLE LIFE AND STORAGE

When stored at or below 50°C in the original unopened containers, this product has a usable life of 12 months From the date of production.

7. LIMITATIONS

This product is neither tested nor represented as suitable for medical or pharmaceutical uses. This product described herein have been designed, manufactured and developed solely for general industrial use only.

8. LIMITED WARRANTY INFORMATION : PLEASE READ CAREFULLY

The information contained herein is offered in good faith and is believed to be accurate. However, because Conditions and methods of use of our products are beyond our control, this information should not be used in Substitution for customer's tests to ensure that Grace Continental Korea's products are safe, effective, and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

Grace Continental Korea specifically disclaims any other express or implied warranty of fitness for a particular Purpose or merchantability.

Grace Continental Korea disclaims liability for any incidental or consequential damages.

101-303, Bucheon Techno-Park, 364, SamjakRo, Ojeong-Gu, Bucheon-Si, Gyeonggi-Do, South Korea
Web Site : www.gckorea.com

TEL 82-32-328-0121 / FAX 82-32-328-0128

- Sales : info@gckorea.com / sales@gckorea.com

- R&D Institute : rnd@gckorea.com
